

Richardson Gratings™ 1200 Grooves, 25 x 25mm, 300nm, Plane Ruled Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings



Stock **#37-135** ☐ In Stock

1

C\$235.20

ADD TO CART

Qty 1+

C\$235.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Groove Density (grooves/mm):
1200

Wavelength Range (nm):
200 - 1200

Blaze Wavelength (nm):
300 ±25

Blaze Angle (°): 10.4
Peak Efficiency, Typical (%): 85
Dimensions (mm): 25.0 x 25.0 ±0.1
Clear Aperture (%): >90
Coating: Aluminium
Construction: Ruled Grating
Length (mm): 25.00
Substrate: ☐ Float Glass
Thickness (mm): 6.00 ±0.5
Type: Reflective Diffraction Grating
Width (mm): 25.00
Reflected Wavefront, RMS: λ/4
Centering of Ruled Area on Substrate (mm): ±1
Alignment of Grooves to Edge (°): ±0.15
Groove Spacing Tolerance (%): <0.05
Polarization: S and P
Master Reference: 0990
Spectral Order (m): 1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View