

TECHSPEC® 12.0mm Dia. x -15 FL, YAG-BBAR, Plano-Concave Lens



Stock **#21-311** ☐ In Stock

-

1

+

C\$62.30

ADD TO CART

Qty 1-9
C\$62.30
Qty 10+
C\$56.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.00

Effective Focal Length EFL (mm):
-15.00

Substrate: N-SF11
f/#: 1.00
Numerical Aperture NA: 0.40
Coating: YAG-BBAR (500-1100nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 500 - 1100
Back Focal Length BFL (mm): -16.68
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.00 ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 11.00
Coating Specification: R_{abs} <0.25% @ 532nm R_{abs} <0.25% @ 1064nm R_{avg} <1.0% @ 500 - 1100nm
Edge Thickness ET (mm): 4.47
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -11.77
Surface Quality: 40-20
Damage Threshold, By Design: 5 J/cm² @ 532nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant