

TECHSPEC[®] 12.0mm Dia. x 72.0mm FL, VIS 0° Coated, Plano-Convex Lens



Stock **#47-339** ☐ In Stock
[Other Coating Options](#)

-

1

+

C\$58.10

ADD TO CART

Qty 1-9

C\$58.10

Qty 10+

C\$52.15

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.00 +0.0/-0.025

Effective Focal Length EFL (mm):
72.00 @ 587.6nm

Back Focal Length BFL (mm): 70.42
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.40 ±0.05
Edge Thickness ET (mm): 1.91
Radius R₁ (mm): 37.21
Clear Aperture CA (mm): 11
f/#: 6
Numerical Aperture NA: 0.08
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, Reference: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View