

TECHSPEC® 12.5" Diameter x 75" FL Protected Gold, Parabolic Mirror



Stock **#32-276-566** [CONTACT US](#)

- 1 + **C\$4,781.00**

ADD TO CART

Qty 1-2
C\$4,781.00
Qty 3+
C\$4,064.20
Volume Pricing
Request Quote

Get Product Downloads

Substrate: [BOROFLOAT®](#)[SUPREMAX®](#)

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 12.5 +0.06/-0
Diameter (mm): 317.50 +1.5/-0
Effective Focal Length EFL (inches): 75.0
Effective Focal Length EFL (mm): 1,905.00
Radius of Curvature (mm): 3,810.00
Aperture (f/#): f/6
Coating: Protected Gold (700-10000nm)
Coating Specification: Ravg >96% @ 700 - 2000nm Ravg >96% @ 2000 - 10,000nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 286
Edge Thickness ET (inches): 2.13
Edge Thickness ET (mm): 54.10
Type: Parabolic Mirror
Wavelength Range (µm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference: 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant