

[See all 7 Products in Family](#)

1.25", Green 530nm, High Intensity Pattern Projecting Spot Light

See More by [Advanced Illumination](#)



Advanced Illumination High Intensity Pattern Projecting Spot Lights

Stock **#18-636** **2 In Stock**

⊖ 1 ⊕ C\$1,435⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$1,435.00 each
Need More?	Request Quote

Product Downloads

General

SL256-530IC **Model Number:**

50000 **LED Lifetime (hours):**

LED Illuminator **Type of Illumination:**

Note:
Optional Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are Available

Advanced Illumination

Manufacturer:

Spot Light

Geometry:

Constant

Illumination Mode:

Physical & Mechanical Properties

1.25

Diameter (inches):

413

Weight (g):

20.8

Diameter of Compatible Reticle (mm):

Optical Properties

Green

Color:

530

Wavelength (nm):

Electrical

0.592

Minimum Input Current:

Hardware & Interface Connectivity

Flying Leads

Connector:

Power Supply:
Power Supply Required and Sold Separately.
USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#89-513](#)
Korea: [#33-773](#)
China: [#66-855](#)

2

Length of Cable (m):

Environmental & Durability Factors

0 - 50

Operating Temperature (°C):

IP50

Environmental Rating:

Regulatory Compliance

[Exempt](#)

RoHS 2015:

[View](#)

Certificate of Conformance:

[Contains SVHC\(s\)](#)

Reach 233:

Product Details

- Intense Output up to 2,000 Lux
- Includes Heat Sink for Thermal Management
- Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended
- Compatible [Reticles](#) Also Available

Advanced Illumination High Intensity Pattern Projecting Spot Lights offer clusters of high intensity LEDs up to 2,000 lux for focused, homogenous illumination. The spot lights are constructed with a large heat sink, improving thermal management to facilitate increased brightness while maintaining safe operating temperatures. For ease of integration, these LED light projectors are compatible with our [full selection of 21mm diameter reticles](#), including crosshair, concentric circles, and net grid. Advanced Illumination High Intensity Pattern Projecting Spot Lights are compatible with 2/3" format C-Mount lenses and are ideal for machine vision inspection applications, such as edge detection, locating offsets, and assessing topography.

Note: Requires 24V power supply [#66-855](#). Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are recommended and sold separately.