


# TECHSPEC® 12.5 x 17.5mm Silver, 4-6λ Mirror



Stock #89-472 [CONTACT US](#)

1

C\$46<sup>.90</sup>

**ADD TO CART**



Volume Pricing	
Qty 1-5	C\$46.90 each
Qty 6-25	C\$35.00 each
Qty 26-99	C\$33.60 each
Need More?	<a href="#">Request Quote</a>

Product Downloads	
STEP:step	Curve:pdf
PDF Drawing:pdf	IGES:igs
eDrawing:eprt	
EO Spec Sheet	<a href="#">Download All</a>

## General

**Type:** Flat Mirror

## Physical & Mechanical Properties

<b>Thickness (mm):</b> 2.00	<b>Dimensions (mm):</b> 12.5 x 17.5
<b>Clear Aperture CA (mm):</b> 11.50 x 16.50	<b>Dimensional Tolerance (mm):</b> ±0.25
<b>Edges:</b> Seamed, 0.5mm Maximum Edge Chip	<b>Length (mm):</b> 17.50
<b>Width (mm):</b> 12.50	

## Optical Properties

<b>Coating Type:</b> Metal	<b>Coating:</b> Protected Silver (450-10000nm)
<b>Surface Flatness (P-V):</b> 4 - 6λ	<b>Wavelength Range (nm):</b> 450 - 10000
<b>Substrate:</b> Float Glass	<b>Coating Specification:</b> R <sub>avg</sub> >98% @ 450 - 2000nm R <sub>avg</sub> >98% @ 2000 - 10,000nm
<b>Surface Quality:</b> 60-40	<b>Damage Threshold, Reference:</b> 0.5 J/cm <sup>2</sup> @ 532nm & 1064nm, 10ns

## Regulatory Compliance

RoHS 2015: [Compliant](#)

Certificate of Conformance: [View](#)

## Product Details

- Wide Variety of Shapes and Sizes Available
- Enhanced Aluminum, Protected Gold, and Protected Silver Coatings for high reflectivity from 450-10000nm
- **Contact Us** for Custom Sizes

TECHSPEC® First Surface Mirrors feature a high reflectivity coating deposited on the front surface of the glass substrate. The mirrors are available in enhanced aluminum, protected gold, and protected silver coatings for high reflectivity from 450-10000nm. The coated surface should be oriented to reflect incident light. TECHSPEC First Surface Mirrors are offered in circular, square, and rectangular dimensions. First surface mirrors are ideal for applications requiring the mirror to be mounted at 45° in order to produce a 90° bend in the light path. These first surface mirrors easily mount into a [range of optical mounts](#) to facilitate application integration.

Note: A range of mounts specifically compatible with individual TECHSPEC® First Surface Mirrors can be found on product web pages.

TECHSPEC® First Surface Mirrors feature a high-reflectivity coating deposited on the front surface of a float-glass substrate to minimize ghosting and enable accurate beam redirection.

They are available with enhanced aluminum, protected silver, and protected gold coatings for applications requiring high reflectivity from 450 – 10000nm.

These mirrors are ideal for optical path folding, beam steering, and imaging systems where the mirror is mounted at 45° to produce a 90° bend in the light path.

Offered in circular, square, and rectangular formats, they are well-suited for OEM integration, prototype builds, and general laboratory alignment setups. With typical surface flatness of 4 – 6λ (waves) and 60-40 surface quality, they provide a cost-effective solution for applications that require reliable reflected beam performance without the added expense of precision polished substrates.


First-surface mirrors are commonly used in life sciences, metrology, semiconductor, and general photonics systems where the quality of reflected light is important.

For proper use, the coated surface should be oriented toward the incident light to avoid transmission through the substrate and preserve optical performance.

## Technical Information

### Coating Curves

Protected Silver (450-10000nm) - R <sub>s</sub> 45°
Protected Silver (450-10000nm) - R <sub>p</sub> 45°
Protected Silver (450-10000nm) - R(avg) 45°
Protected Silver (450-10000nm) - R @ 0°



Please note that coating performance outside each product's specified design range is theoretical and may vary.

## Related Products



PUROSOL™ Optical Cleaner



λ/4 First Surface Mirrors



4-6λ First Surface Mirrors




Optical Mirror Mounts

## Frequently Purchased Together




#31-417 - 17 x 23mm, 4-6λ Mirror  
C\$29.75

Qty




#02-105 - 12.5mm Diameter Float Glass Window  
C\$21.00

Qty



#30-935 - 1.0 OD 25mm Diameter, Reflective ND Filter  
C\$83.93

Qty



#30-938 - 2.0 OD 25mm Diameter, Reflective ND Filter  
C\$83.93

Qty

## Compatible Mounts

	Title	Type	Compare	Stock Number	Price	Buy
	1.5" Reverse Angle Mirror Mount	Adjustable - Tip-Tilt		#37-922	C\$120.40 <a href="#">Request Quote</a>	20+ In Stock <input type="text" value="1"/>
	25mm sq - Rectangular Bar Clamp	Fixed		#54-994	C\$151.20 <a href="#">Request Quote</a>	8 In Stock <input type="text" value="1"/>
	60mm sq - Rectangular Bar Clamp	Fixed		#54-995	C\$176.40 <a href="#">Request Quote</a>	20+ In Stock <input type="text" value="1"/>
	Standard Model, Threaded Base - Metric Mirror Mount	Adjustable - Tip-Tilt		#56-341	C\$196.00 <a href="#">Request Quote</a>	20+ In Stock <input type="text" value="1"/>
	Standard Model, Slotted Base - Metric Mirror Mount	Adjustable - Tip-Tilt		#56-342	C\$196.00 <a href="#">Request Quote</a>	20+ In Stock <input type="text" value="1"/>
	Top-Screw Model, Threaded Base - Metric Mirror Mount	Adjustable - Tip-Tilt		#56-343	C\$260.40 <a href="#">Request Quote</a>	4 In Stock <input type="text" value="1"/>
	Top-Screw Model, Slotted Base - Metric Mirror Mount	Adjustable - Tip-Tilt		#56-344	C\$260.40 <a href="#">Request Quote</a>	20+ In Stock <input type="text" value="1"/>

# Resources

## Media Type

- Application Note
- Video
- FAQ
- Glossary

📄 CASE STUDIES

Laser Optics  
for Eye  
Surgery

↑ TRENDING IN OPTICS

Increasing  
Challenges for  
Sourcing Laser  
Optics...

📄 CASE STUDIES

Using IR  
Spectroscopy  
for Counterfeit  
Drug Detection

📄 APPLICATION NOTE

Metallic Mirror  
Coatings

▶ VIDEO

Optical Mirrors  
Review

? FAQ

What is the  
difference  
between a  
first-surface...

[View More](#)