


TECHSPEC[®]

12.5 x 12.5mm, 0.13 Numerical Aperture, Uncoated, Square Precision Aspheric Lens



Stock #17-312 ☐ In Stock

- 1 +

C\$455.00

ADD TO CART

Qty 1-5

C\$455.00

Qty 6+

C\$364.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Dimensions (mm):
12.50 x 12.50

Effective Focal Length EFL (mm):
50.00 @ 587.6nm

Numerical Aperture NA:
0.13

Back Focal Length BFL (mm): 45.23
Substrate: N-BK7
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 11.50 x 11.50
Edge Thickness ET (mm): 6.48
Center Thickness CT (mm): 7.24 ±0.10
f#: 4.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 350 - 2200
Conjugate Distance: Infinite
Power (diopters): 20.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View