

TECHSPEC® 12.5mm Dia., 0.63 NA, 350-700nm Coated, NIR Aspheric Lens



TECHSPEC® Near-Infrared (NIR) Aspheric Lenses

Stock **#16-267** ☐ In Stock

[Other Coating Options](#)

-

1

+

C\$294.00

ADD TO CART

Qty 1-5

C\$294.00

Qty 6+

C\$235.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50 +0.00/-0.10

Effective Focal Length EFL (mm):
10.00 @ 780nm

Numerical Aperture NA:
0.63

Back Focal Length BFL (mm): 7.61
Substrate: S-LAH64
Aspheric Design Wavelength (nm): 780
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: VS+ (350-700nm)
Coating Specification: R _{avg} < 0.5% @ 350 - 700nm @ 0° ±30° AOI R _{abs} < 1.5% @ 350 - 700nm @ 0° ±30° AOI
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 11.25
Edge Thickness ET (mm): 1.60
Center Thickness CT (mm): 4.25 ±0.10
f/#: 0.80
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Conjugate Distance: Infinite
Power (diopters): 100.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View