

TECHSPEC[®] 12.5mm Dia, 0.66 Numerical Aperture NIR Coated, Aspheric Lens



Stock #69-862 ☐ In Stock
[Other Coating Options](#)

-

1

+

C\$301.00

ADD TO CART

Qty 1-5

C\$301.00

Qty 6+

C\$240.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.1

Effective Focal Length EFL (mm):
9.50 @ 587.6nm

Numerical Aperture NA:
0.66

Back Focal Length BFL (mm): 6.51
Substrate: N-SF5
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: BBAR (600-1050nm)
Coating Specification: R _{avg} ≤1.5% @ 600 - 1050nm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 11.25
Edge Thickness ET (mm): 1.60
Center Thickness CT (mm): 5.00 ±0.1
f/#: 0.76
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Power (diopters): 105.26

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant