

TECHSPEC[®] 12.5mm Dia. 1° Nom. Fused Silica Wedge Prism 1064nm Laser V-Coat



TECHSPEC Fused Silica Wedge Prisms

Stock #39-124 ☐ In Stock

-

1

+

C\$203.00

ADD TO CART

Qty 1-5

C\$203.00

Qty 6+

C\$162.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:
Laser V-Coat (1064nm)

Angle Tolerance (arcsec):
30

Bevel:
Protective bevel as needed

Coating Specification: R_{abs} <0.25% @ 1064nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52
Design Wavelength DWL (nm): 1064
Diameter (mm): 12.50
Image Orientation: Beam Deviation
Power (diopters): 1.74
Ray Deviation @ 355nm (°): 1.00
Substrate: Fused Silica (Corning 7980)
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Thickness (mm): 1.50
Wedge Angle: 2° 5'56"
Damage Threshold, By Design: 15 J/cm² @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View