

**TECHSPEC® 125mm, Center Drive, Standard Top, Metric Stage**



TECHSPEC® Crossed-Roller Bearing Linear Translation Stages (Standard-Top Model)



Stock #66-456 **1 In Stock**

⊖ 1 ⊕ C\$931<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-2	C\$931.00 each
Qty 3+	C\$812.70 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Metric **Type:**

**Physical & Mechanical Properties**

Linear (X) **Type of Movement:**

**Guide System:**



**30mm Standard-Top Stages - Center Drive**



**30mm Standard-Top Stages - Side Drive**



**40mm Standard-Top Stages - Center Drive**



**40mm Standard-Top Stages - Side Drive**



**70mm Standard-Top Stages - Center Drive**



**70mm Standard-Top Stages - Side Drive**



**125mm Standard-Top Stages - Center Drive**



**125mm Standard-Top Stages - Side Drive**

