

TECHSPEC® 12.5mm Dia. 2.5° Nom. Fused Silica Wedge Prism 355nm Laser V-Coat



TECHSPEC Fused Silica Wedge Prisms

Stock **#39-077** CLEARANCE ☐ In Stock

-

1

+

C\$132.93

ADD TO CART

Qty 1+

C\$132.93

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:
Laser V-Coat (355nm)

Angle Tolerance (arcsec):
30

Bevel:
Protective bevel as needed

Coating Specification:
Rabs <0.25% @ 355nm

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

0.52
Design Wavelength DWL (nm): 355
Diameter (mm): 12.50
Image Orientation: Beam Deviation
Power (diopters): 4.37
Ray Deviation @ 355nm (°): 2.50
Substrate: ☐ Fused Silica (Corning 7980)
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Thickness (mm): 1.50
Wedge Angle: 5° 13'29"
Damage Threshold, By Design: ☐ 7.5 J/cm² @ 355nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View