


TECHSPEC[®] 12.5mm Dia. 2° Nom. Fused Silica Wedge Prism Uncoated



TECHSPEC Fused Silica Wedge Prisms

Stock **#35-845** CLEARANCE ☐ In Stock

-

1

+

C\$103.53

ADD TO CART

Qty 1+

C\$103.53

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:

Uncoated

Angle Tolerance (arcsec):

30

Bevel:

Protective bevel as needed

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

0.52

Design Wavelength DWL (nm):

355
Diameter (mm): 12.50 +0.00/-0.10
Image Orientation: Beam Deviation
Power (diopters): 3.49
Ray Deviation @ 355nm (°): 2.00
Substrate:  Fused Silica (Corning 7980)
Surface Quality: 20-10
Thickness (mm): 1.50
Type: Wedge Prism
Wavelength Range (nm): 200 - 2200
Wedge Angle: 4° 11'14"
Note: Specificy this is S1 & S2 power and irregularity, not the overall power of the wedge
Power (fringes) @ 632.8nm: 0.50
Irregularity (fringes) @ 632.8nm: 0.20

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View