


TECHSPEC[®] 12.5mm Dia. 1° Beam Dev. Fused Silica Wedge Prism 355nm Laser V-Coat



TECHSPEC Fused Silica Wedge Prisms

Stock **#39-074** CLEARANCE **5 In Stock**

-

1

+

C\$145⁶⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$145.60 each
Need More?	Request Quote

Product Downloads

General

Note:
Specifcy this is S1 & S2 power and irregularity, not
the overall power of the wedge

Physical & Mechanical Properties

Diameter (mm):
12.50

Thickness (mm):
1.50

Bevel:
Protective as needed

Wedge Angle (arcmin):		2° 5'55"
Optical Properties		
Angle Tolerance (arcsec):		30
Coating:		Laser V-Coat (355nm)
Design Wavelength DWL (nm):		355
Substrate: ☐		Fused Silica (Corning 7980)
Surface Quality:		20-10
Image Orientation:		Beam Deviation
Coating Specification:		R _{abs} <0.25% @ 355nm
Damage Threshold, By Design: ☐		7.5 J/cm ² @ 355nm, 20ns, 20Hz
Power (fringes) @ 632.8nm:		0.50
Irregularity (fringes) @ 632.8nm:		0.20
Ray Deviation @ 355nm (°):		1.00
Power (diopters):		1.74
Wedge Angle (°):		2.1°

Material Properties	
Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):	
0.52	

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 209:
View	Certificate of Conformance:


Product Details


- Deviates Laser Beam Path from 0.5° - 5.0°
- Ideal for UV to NIR Beam Steering Applications from 250 to 1064nm
- Ideal for High Power Beam Steering Applications

TECHSPEC® Fused Silica Wedge Prisms are designed for a range of laser beam steering applications requiring UV-VIS or first through fourth Nd:YAG harmonic Anti-Reflection Coatings. They are optimized to ensure the highest level of system performance using tightly controlled specifications including *N*/10 surface flatness, 20-10 surface quality, and a wedge tolerance of 15 or 30 arcseconds. The Nd:YAG coated versions feature high transmittance and guaranteed laser damage thresholds specific to the design wavelength. TECHSPEC® Fused Silica Wedge Prisms utilize a wedge design to deviate laser beam path from 0.5° – 5°. By creating a risley prism pair using two wedge prisms with the same ray deviation, custom beam steering up to two times the wedge deviation is possible. A low coefficient of thermal expansion ensures accurate beam steering in high power laser applications.

Note: Power Diopter is defined as 1cm deviation at a distance of 1m from the prism. TECHSPEC® Wedge Prisms are also available in [N-BK7 versions](#).

Technical Information





Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
