


12.5mm Dia. High Contrast VIS-NIR Polarizer



Stock **#36-652** 5 In Stock

-

1

+

C\$525^{.00}

ADD TO CART

Volume Pricing	
Qty 1-9	C\$525.00 each
Qty 10+	C\$498.40 each
Need More?	Request Quote

Product Downloads

General

Type:

Linear Polarizer

Physical & Mechanical Properties

Clear Aperture CA (mm):

11.25

Diameter (mm):

12.50

Thickness (mm):

2.00 ±0.2

+0.0/-0.2	Dimensional Tolerance (mm):
	Construction:
Nanoparticle	
	Clear Aperture (%):
90	

Optical Properties	
	Angle of Incidence (°):
±20	
	Extinction Ratio:
>10,000:1 (650nm - 850nm) >1,000:1 (650nm - 1000nm)	
	Substrate: ☐
Soda Lime Float Glass	
	Surface Quality:
40-20	
	Transmission (%):
>84	
	Transmitted Wavefront, P-V:
< λ/4	
	Beam Deviation (arcmin):
<1	
	Polarization Axis Mark (%):
±2	
	Wavelength Range (nm):
600 - 1000	

Environmental & Durability Factors	
	Operating Temperature (°C):
-20 to +120	

Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	REACH 241:
Compliant	

Product Details

- Multiple Wavelength Ranges for UV, VIS and NIR
- >100,000:1 Contrast Ratios Available
- Ideal for Use in Harsh Environments

UV, VIS-NIR, and NIR High Contrast Polarizers offer both versatility and performance over a wide range of wavelengths. These polarizers contain uniformly stretched silver nano-particles in a 220 ±25µm thick soda-lime glass laminated on a thicker soda-lime substrate for increased durability. UV, VIS-NIR, and NIR High Contrast Polarizers are ideal for harsh environments, can withstand up to 120°C, are resistant to UV-radiation and chemicals, and can be safely used in humid environments.

Technical Information

