

TECHSPEC® 12.5mm Dia. x 30mm FL, MgF₂ Coated, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock **#32-313** ☒ In Stock

☐ [Other Coating Options](#)

1

C\$106.40

ADD TO CART

Qty 1-5

C\$106.40

Qty 6+

C\$85.05

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50 +0.0/-0.025

Effective Focal Length EFL (mm):

30.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 26.12
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 11.50
Centering (arcmin): <1
Center Thickness CT (mm): 5.70 ±0.10
Center Thickness CT 1 (mm): 4.50 ±0.05
Center Thickness CT 2 (mm): 1.20 ±0.05
Radius R ₁ (mm): 15.97
Radius R ₂ (mm): -15.00
Radius R ₃ (mm): -528.23
Edge Thickness ET (mm): 4.39
Substrate:  N-SSK8 / N-SF10
Surface Quality: 40-20
f/#: 2.4
Numerical Aperture NA: 0.21
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant