


TECHSPEC[®] 12.5mm Dia x 10mm FL Acylinder Lens, Uncoated



TECHSPEC Acylinder Lenses

Stock **#86-030** 20+ In Stock

-

1

+

C\$954⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$954.80 each
Qty 6-25	C\$764.40 each
Qty 26-49	C\$702.80 each
Need More?	Request Quote

Product Downloads

General	
Acylinder Lens	Type:
Physical & Mechanical Properties	
12.50 +0.0/-0.1	Diameter (mm):
6.00	Center Thickness CT (mm):

±0.1	Center Thickness Tolerance (mm):
90.00	Clear Aperture (%):
2.8	Edge Thickness ET (mm):
Optical Properties	
10.00	Effective Focal Length EFL (mm):
N-SF5	Substrate: □
0.8	f/#:
0.63	Numerical Aperture NA:
Uncoated	Coating:
380 - 2500	Wavelength Range (nm):
6.4	Back Focal Length BFL (mm):
587.6	Focal Length Specification Wavelength (nm):
1.0	Surface Accuracy, RMS (µm):
60-40	Surface Quality:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 219:
View	Certificate of Conformance:

Product Details

• Diffraction Limited Design

• Ideal for Creating Thin Line Profiles of Monochromatic Light Sources

• Focus Light in Single Dimension

TECHSPEC® Acylinder Lenses are similar to aspheric lenses in that they provide diffraction-limited focusing performance in only one dimension. By reducing spherical aberration along the focusing axis, TECHSPEC® Acylinder Lenses are ideal for creating thin line profiles. Compared to standard cylinder lenses, TECHSPEC® Acylinder Lenses also dramatically reduce the spot size of monochromatic light sources to provide sharp, thin lines.

LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

Technical Information

