

TECHSPEC® 12.5mm Dia. x 80mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#49-331-INK** 3-5 DAYS

[Other Coating Options](#)

- 1 + **C\$134.40**

ADD TO CART

Qty 1-5
C\$134.40
Qty 6+
C\$107.45
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 ±0.025

Effective Focal Length EFL (mm):
80.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 78.40
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 11.50
Centering (arcmin) : <1
Center Thickness CT (mm) : 3.70 ±0.10
Center Thickness CT 1 (mm) : 2.10 ±0.05
Center Thickness CT 2 (mm) : 1.60 ±0.05
Radius R₁ (mm) : 49.62
Radius R₂ (mm) : -35.73
Radius R₃ (mm) : -103.22
Edge Thickness ET (mm) : 3.12
Substrate : ☐ N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 6.4
Numerical Aperture NA : 0.08
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS 2015 : Compliant
REACH 201 : Compliant
Certificate of Conformance : View