

TECHSPEC® 12.5mm Dia. x 20mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#49-322-INK** ☒ In Stock
[Other Coating Options](#)

1 **C\$134.40**

ADD TO CART

Qty 1-5
C\$134.40
Qty 6+
C\$107.45
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 ±0.025

Effective Focal Length EFL (mm):
20.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 16.45
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 11.50
Centering (arcmin) : <1
Center Thickness CT (mm) : 10.50 ±0.10
Center Thickness CT 1 (mm) : 5.25 ±0.05
Center Thickness CT 2 (mm) : 5.25 ±0.05
Radius R₁ (mm) : 13.98
Radius R₂ (mm) : -9.35
Radius R₃ (mm) : -76.14
Edge Thickness ET (mm) : 4.62
Substrate : ☐ S-BAH11 / N-SF10
Surface Quality : 40-20
f/# : 1.6
Numerical Aperture NA : 0.31
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View