

TECHSPEC® 12.5mm Dia x 25mm FL NIR I Coated, Illumination Grade PCX Cylinder Lens



Stock **#69-743** ☐ In Stock

-

1

+

C\$114.80

ADD TO CART

Qty 1-5
C\$114.80
Qty 6+
C\$91.70
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50

Effective Focal Length EFL (mm):
25.00

Substrate: ☐
[N-BK7](#)

f/#:

Numerical Aperture NA: 0.25
Coating: NIR I (600-1050nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 600 - 1050
Back Focal Length BFL (mm): 23.09
Center Thickness CT (mm): 2.90
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.29
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 12.96
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant