

TECHSPEC® 12.5mm Dia. x 60mm FL, VIS 0°, Inked, Achromatic Lens



Stock **#47-668-INK** ☒ In Stock
[Other Coating Options](#)

1 **C\$127.40**

ADD TO CART

Qty 1-5
C\$127.40
Qty 6+
C\$101.85
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50 ±0.025

Effective Focal Length EFL (mm):
60.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 57.59
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 11.50
Centering (arcmin): <1
Center Thickness CT (mm): 5.00 ±0.10
Center Thickness CT 1 (mm): 3.50 ±0.05
Center Thickness CT 2 (mm): 1.50 ±0.05
Radius R₁ (mm): 36.51
Radius R₂ (mm): -26.33
Radius R₃ (mm): -78.35
Edge Thickness ET (mm): 4.21
Substrate: ☐ N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 4.8
Numerical Aperture NA: 0.10
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View