

TECHSPEC®

12.5mm H x 25mm L x 75mm FL NIR I Coated, Illumination Grade PCX Cylinder Lens



Stock #69-750 ☐ In Stock

-

1

+

C\$114.80

ADD TO CART

Qty 1-5
C\$114.80
Qty 6+
C\$91.70
Volume Pricing
Request Quote

Get Product Downloads



Effective Focal Length EFL (mm):
75.00

Substrate: ☐
[N-BK7](#)

f/#:
6

Numerical Aperture NA: 0.08
Coating: NIR I (600-1050nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 600 - 1050
Back Focal Length BFL (mm): 73.68
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 12.5 x 25.0
Edge Thickness ET (mm): 1.49
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 38.76
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 7 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant