

1/2",5mm,F1.4,C-mount,ViSWIR Singleband



Computar ViSWIR Lite Lenses

Stock **#74-611** NEW **2 In Stock**

-

1

+

C\$1,463⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$1,463.00 each
Need More?	Request Quote

Product Downloads

General

Model Number:	
H0514-VSW	
Imaging Lens Type:	
Fixed Focal Length SWIR Lens	

Physical & Mechanical Properties

Iris Option:	
Manual Iris	
Length (mm):	
45.50	

44.5	Maximum Diameter (mm):
32.00	Outer Diameter (mm):
102.0	Weight (g):
7.00	Maximum Rear Protrusion (mm):
45.5	Maximum Length (mm):

Optical Properties	
65.5°	Horizontal Field of View @ Max Sensor Format:
65.5° (H6.4)	Horizontal Field of View, 1/2" Sensor:
35.3° (H3.2)	Horizontal Field of View, 1/4" Sensor:
8.20	Maximum Image Circle (mm):
400 - 1700	Wavelength Range (nm):
5.00	Focal Length FL (mm):
100 - 900	Working Distance (mm):
Horizontal: 65.5° Vertical: 51.4° Diagonal: 76.7°	FOV @ Max Sensor Format, H x V (mm):
f/1.4	Aperture (f/#):
10.8	Back Focal Length BFL (mm):
14.99	Entrance Pupil Position (mm):
20.25	Object Space Principal Plane (mm):
5.08	Image Space Principal Plane (mm):
-0.48	Maximum Distortion (%):
147.4307	Exit Pupil Position (mm):
VIS-SWIR	Lens Wavelength Range:
VIS, SWIR	Wavelength:

Sensor	
1/2"	Optimized Sensor Format:
1/2"	Maximum Sensor Format:
1.50	Resolution (Megapixels):

Threading & Mounting	
M43 x0.75	Filter Thread:
C-Mount	Mount:

Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Outstanding Cost to Performance Ratio from the VIS to SWIR
- 1.5 MegaPixels, 1/2" or 2/3", C-Mount
- Focal Lengths Ranging from 5 - 50mm

Computar ViSWIR Lite Lenses are compact lenses that deliver outstanding cost-performance for single-wavelength lighting and narrow-band imaging. Utilizing a multilayer coating that absorbs specific wavelengths to minimize adverse lighting effects, these lenses ensure precise imaging is achieved. The broadband anti-reflection coating offers high and stable transmission across a wide wavelength range from 400nm to 1,700nm. Computar ViSWIR Lite

Lenses are available in 1/2" and 2/3" sensor formats, an easily integratable C-mount design, and focal lengths that range from 5 to 50mm. These lenses are ideal for non-visible range imaging in applications across Agricultural, Medical, and Remote Sensing industries.
