

**TECHSPEC®**

**12.5mm H x 25mm L x -100mm FL Uncoated, Illumination Grade PCV Cylinder Lens**



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock **#68-058** **20+ In Stock**

⊖ 1 ⊕ C\$106<sup>40</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	C\$106.40 each
Qty 6-25	C\$95.90 each
Qty 26-49	C\$91.00 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Cylinder Lens, Plano-Concave **Type:**

**Physical & Mechanical Properties**

2.50 **Center Thickness CT (mm):**

**Center Thickness Tolerance (mm):**

±0.1

**Dimensional Tolerance (mm):**

+0.0/-0.2

**Dimensions (mm):**

12.5 x 25.0

**Edge Thickness ET (mm):**

2.84

## Optical Properties

**Effective Focal Length EFL (mm):**

-100.00

**Substrate:**

[N-BK7](#)

**Coating:**

Uncoated

**Wavelength Range (nm):**

350 - 2200

**Back Focal Length BFL (mm):**

-101.65

**Focal Length Tolerance (%):**

±3

**Radius R<sub>1</sub> (mm):**

-51.68

**Surface Quality:**

60-40

## Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**REACH 201:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)


## Product Details

- Cylinder Lenses Ideal for 1 Dimensional Laser Beam Convergence
- Circular and Rectangular Form Factors
- Multiple Coating Options Available

TECHSPEC® Illumination Grade PCV Cylinder Lenses are commonly used to turn a collimated laser source into a line generator. These PCV Cylinder Lenses and [TECHSPEC Illumination Grade PCX Cylinder Lenses](#) can be used together for beam expander applications.

The thin lens approximation for the length of a line generated by a negative cylinder lens is:  $L = 2 * (r_0/f) * (z + f)$  where L is the line length,  $r_0$  is half the beam diameter, z is the projection distance, and -f is the focal length of the lens.

## Technical Information



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).