


TECHSPEC® 12.7 x 12.7mm Protected Silver, 4-6λ Mirror



Stock **#36-041** ☐ In Stock

- 1 +

C\$39.20

ADD TO CART

Qty 1-5
C\$39.20
Qty 6+
C\$30.10
Volume Pricing
Request Quote

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensions (mm):
12.7 x 12.7

Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >98% @450 - 2000nm R _{avg} >98% @2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 11.70 x 11.70
Edges: Seamed, 0.5mm Maximum Edge Chip
Thickness (mm): 2.00
Type: Flat Mirror
Wavelength Range (nm): 450 - 10000
Length (mm): 12.70
Width (mm): 12.70
Damage Threshold, By Design: ☐ 0.5 J/cm ² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant