

TECHSPEC® 12.7 x 25.4mm EFL 90° Protected Aluminum 100Å Off-Axis Parabolic Mirror



Stock **#35-482** ☐ **In Stock**

[Other Coating Options](#)

1

C\$252.00

ADD TO CART

Qty 1-5
C\$252.00
Qty 6+
C\$226.80
Volume Pricing
Request Quote

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
12.70 +0.00/-0.38

Effective Focal Length EFL (mm):
25.40

Focal Length Tolerance (%) : ±1
Radius of Curvature (mm) : 25.40
Coating : Protected Aluminum (400-2000nm)
Coating Type : Metal
Coating Specification : R _{avg} ≥85% @400 - 700nm R _{avg} ≥97% @2,000 - 12,000nm
Off-Set Angle (°) : 90
Parent Focal Length PFL (mm) : 12.7
Surface Figure, RMS : λ/4
Surface Roughness (Angstroms) : <100 RMS
Wavelength Range (nm) : 400 - 2000
Clear Aperture (%) : 90
Surface Quality : 80-50
Compatible Mounting Plates : #34-425
Substrate : Aluminum 6061-T6
Y Offset (mm) : 25.4
Reflected Wavefront, RMS : λ/2

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant