


[See all 1 Products in Family](#)

12.7mm Dia., 2mm Thick, Uncoated, ISP Optics Quartz Window | Q-W-12-2

See More by [ISP Optics](#)



Stock #24-595 **CLEARANCE** 3 In Stock

⊖ 1 ⊕ C\$144¹³

ADD TO CART

Volume Pricing

Qty 1+	C\$144.13 each
Need More?	Request Quote

Product Downloads

General

Q-W-12-2 **Model Number:**

Protective Window **Type:**

Glass **Type of Window:**

Physical & Mechanical Properties

10.79 **Clear Aperture CA (mm):**

12.70 +0.00/-0.13	Diameter (mm):
2.00 ±0.13	Thickness (mm):
<3	Parallelism (arcmin):
Protective as needed	Bevel:
85	Clear Aperture (%):
Fine Ground	Edges:
0.16	Poisson's Ratio:
73	Young's Modulus (GPa):
522.00	Knoop Hardness (kg/mm²):

Optical Properties

Uncoated	Coating:
Quartz	Substrate: □
1.458	Index of Refraction (n_d):
40-20	Surface Quality:
67.8	Abbe Number (v_d):
190 - 3500	Wavelength Range (nm):
1λ per inch @ 633nm	Surface Flatness (P-V):

Material Properties

2.20	Density (g/cm³):
0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- High Transmission from 190 - 3500nm
- High Chemical Resistance
- Low Coefficient of Thermal Expansion

ISP Optics Quartz Windows feature crystalline quartz (SiO₂) substrates, providing high transmission from the UV to the MMR. Unlike fused silica, crystalline quartz does not have hydroxide ion impurities, allowing for its use between 1.4 - 2.7µm with no dips in transmission. The material also has high chemical resistance, a low coefficient of thermal expansion, and relatively high hardness, making these windows advantageous for use in harsh environments or those with fluctuating temperatures. ISP Optics Quartz Windows are ideal for use in UV, visible, or infrared applications as protective windows to protect sensors, lasers, or other electro-optical components.