

TECHSPEC[®] S-Mount, 12.5mm Cube Mount



12.5mm x 17.5mm Plate S-Mount Holder



Stock #11-139 1 In Stock

-

1

+

C\$389⁻²⁰

ADD TO CART

Volume Pricing	
Qty 1-4	C\$389.20 each
Qty 5-9	C\$364.00 each
Qty 10-25	C\$346.36 each
Need More?	Request Quote

Product Downloads

General

Optic Mount (Fixed)

Function:

Cube

Type of Optics:

Note:

Includes one S-Mount Aperture Cap ([# 11-137](#))

Dimensions of Compatible Optics (mm):

12.5 Sq.

Physical & Mechanical Properties

Dimensions (mm):

25.4 x 25.4 x 34.3

Extension Length (mm):

25.4

Min. Thickness of Compatible Optics (mm):

12.5

Max. Thickness of Compatible Optics (mm):

12.5

Threading & Mounting

Thread Type:

S-Mount

Compatible Post:

1/4-20

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

View

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beam Splitters, Filters, and Mirrors
- Provides a 90° Mounting Interface
- ¼-20 and M6 Tapped Mounting Threads for English or Metric Based Systems

TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: #11-139 and #11-142 each include one S-Mount Aperture Cap (#11-137)

Technical Information

