

12.7mm Dia f/0.75 Uncoated, Molded Acrylic Aspheric Lens



Molded Acrylic Aspheric Lenses



Stock **#33-256** ☒ In Stock

1

C\$77.00

ADD TO CART

Qty 1-10	C\$77.00
Qty 11+	C\$63.70
Volume Pricing	Request Quote

Get Product Downloads
Diameter (mm): 12.70 ±0.1
Effective Focal Length EFL (mm): 9.50 @ 632.8nm
Numerical Aperture NA:

0.67
Back Focal Length BFL (mm): 6.4
Substrate: ☐ PMMA
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 632.8
Coating: Uncoated
Clear Aperture CA (mm): 11.4
Edge Thickness ET (mm): 2.00
Center Thickness CT (mm): 6.10
f##: 0.75
Bevel: Protective bevel as needed
Operating Temperature (°C): 80.00
Radius R (mm): 62.23
Type: Aspheric Lens
Wavelength Range (nm): 400 - 1100
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View