


[See all 22 Products in Family](#)

## TECHSPEC® 12.7mm Dia. Precision Broadband Laser Mirror Substrate



TECHSPEC® Laser Mirror Substrates

Stock #75-409 **NEW** 20+ In Stock

1 **C\$119<sup>79</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1-5	<b>C\$119.70</b> each
Qty 6-25	<b>C\$105.00</b> each
Qty 26+	<b>C\$92.40</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Laser Mirror Substrate **Type:**

### Physical & Mechanical Properties

<3 **Parallelism (arcmin):**

90 **Clear Aperture (%):**

Ground	<b>Back Surface:</b>
12.70 +0.0/-0.1	<b>Diameter (mm):</b>
5.00 ±0.2	<b>Thickness (mm):</b>
Ground, protective bevel as needed	<b>Edges:</b>

## Optical Properties

10-5	<b>Surface Quality:</b>
λ/20	<b>Surface Flatness (P-V):</b>
Uncoated	<b>Coating:</b>
<a href="#">Fused Silica</a> (Corning 7980)	<b>Substrate:</b> <input type="checkbox"/>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------

## Product Details

- λ/10 and λ/20 Surface Flatness and 10-5 Surface Quality
- High Quality Fused Silica Substrates
- Imperial Sizes with Circular or Rectangular Geometries
- [Window Substrates](#) Also Available

TECHSPEC® Laser Mirror Substrates are manufactured from high quality fused silica and are designed for use with high power laser sources. These mirrors feature excellent surface specifications, including λ/10 and λ/20 surface flatness and 10-5 surface quality, to limit the possibility of reduced performance due to surface defects. The high surface quality of these mirror blanks also makes them ideal for use in demanding intra-cavity laser applications. TECHSPEC Laser Mirror Substrates are available in standard imperial sizes, with either circular or rectangular geometries. Please contact us if your application requires a custom size laser mirror substrate.