

TECHSPEC[®] 12.7mm Dia. UV, Precision Broadband Laser Mirror



Stock **#48-015** 20+ In Stock

-

1

+

C\$197⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-5	C\$197.40 each
Qty 6-25	C\$173.60 each
Need More?	Request Quote

Product Downloads

General	
Laser Mirror	Type:
Optical Power: <i>N</i> /10	Note:
Physical & Mechanical Properties	
>80	Clear Aperture (%):
Ground	Back Surface:

12.70 +0.0/-0.2	Diameter (mm):
5.00 ±0.1	Thickness (mm):
Optical Properties	
20-10	Surface Quality:
R _{avg} >99% @300 - 550nm	Coating Specification:
300 - 550	Wavelength Range (nm):
λ/10	Surface Flatness (P-V):
λ/20	Irregularity (P-V) @ 632.8nm:
Dielectric	Coating Type:
Dielectric Mirror (300-550nm)	Coating:
0-45	Angle of Incidence (°):
BOROFLOAT®	Substrate: ☐
0.3 J/cm² @ 10ns @ 355nm	Damage Threshold, By Design: ☐

Environmental & Durability Factors	
ML-M-13508-C	Durability:

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	REACH 201:
View	Certificate of Conformance:

Product Details

- Ideal for Tunable Lasers and Reflecting Multiple Laser Sources
 - High Reflectivity from 0 - 45° for All Polarization States
 - Variety of Coating Options Available
- TECHSPEC® Precision Broadband Laser Mirrors feature high reflectivity and are ideal for UV, visible, and NIR beam steering applications. The broadband dielectric enhanced silver coatings feature >98% reflectivity from 450nm to 12μm wavelengths at incident angles from 0 - 45°. These mirrors meet ML-M-13508-C durability standards. [TECHSPEC® Precision Broadband Laser Mirrors](#) are ideal for demanding laser applications requiring high laser damage thresholds including laser scanning and beam steering. The mirrors have a BOROFLOAT® substrate, and are offered in 12.70, 25.40, and 50.80mm diameters.


LASER OPTICS

MADE BY EDMUND OPTICS®



LEARN MORE

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
 - High-precision surface quality and flatness
 - Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts

;