

TECHSPEC® 12.7mm Dia. x 31.8mm FL, Uncoated, Plano-Convex Lens



Stock **#49-843** ☐ In Stock
[Other Coating Options](#)

1 **C\$39.20**

ADD TO CART

Qty 1-9
C\$39.20
Qty 10+
C\$35.35
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.70 +0.0/-0.025

Effective Focal Length EFL (mm):
31.80 @ 587.6nm

Back Focal Length BFL (mm): 29.81
Coating: Uncoated
Substrate:  N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 1.72
Radius R₁ (mm): 16.43
Clear Aperture CA (mm): 11.7
f#: 2.5
Numerical Aperture NA: 0.20
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View