

TECHSPEC®

12.7mm Dia. x 6.35mm 532/630-655/1064nm, Dual Band Laser Mirror



Stock **#26-926** 8 In Stock

-

1

+

C\$247^{.80}

ADD TO CART

Volume Pricing	
Qty 1-5	C\$247.80 each
Qty 6-25	C\$235.20 each
Qty 26-49	C\$222.60 each
Need More?	Request Quote

Product Downloads

General	
Laser Mirror	Type:
Physical & Mechanical Properties	
<3	Parallelism (arcmin):
>90	Clear Aperture (%):

Commercial Polish	Back Surface:
12.70 +0/-0.1	Diameter (mm):
6.35 ±0.10	Thickness (mm):
Optical Properties	
10-5	Surface Quality:
99.5	Reflection at DWL (%):
Coating Specification: R _{avg} ≥99.50% @ 532nm & 1064nm @ 45° AOI R _{avg} ≥80% @ 630 – 655nm @ 45° AOI	
N10	Surface Flatness (P-V):
Dielectric	Coating Type:
Laser Mirror (532, 635, 650, 1064nm)	Coating:
532, 635, 650, 1064	Design Wavelength DWL (nm):
45	Angle of Incidence (°):
Fused Silica (Corning 7980)	Substrate: ☐
Not Specified	Damage Threshold, Reference: ☐

Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- >99% Reflectivity at Design Wavelengths
- 10-5 Surface Quality for Sensitive Laser Applications
- 532/1064nm, 635-670/1064nm, or 800/1030nm Wavelength Bands
- TECHSPEC® Nd:YAG Laser Line Mirrors Also Available

TECHSPEC® Dual Band Laser Line Mirrors feature high reflectivity, excellent surface quality, and precision surface flatness to minimize scattering effects. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in a variety of standard sizes. TECHSPEC® Dual Band Laser Line Mirrors are ideal for beam steering applications in both laboratory and OEM laser systems. These mirrors are available in a 532/1064nm, 635-670/1064nm, and 800/1030nm dual band coating options for Nd:YAG lasers and red and green guide beams.