

[See all 54 Products in Family](#)

TECHSPEC®

12° Beam Dev. VIS-NIR Coated, N-BK7 Wedge Prism



Stock **#47-623** 2 In Stock

-

1

+

C\$96<sup>.60</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | C\$96.60 each                 |
| Qty 6-25       | C\$77.00 each                 |
| Qty 26-49      | C\$72.10 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                                                                                     |                |
|---------------------------------------------------------------------------------------------|----------------|
| Wedge Prism                                                                                 | Type:          |
| Note:<br>Specify this is S1 & S2 power and irregularity, not the overall power of the wedge |                |
| Physical & Mechanical Properties                                                            |                |
| 25.00 +0.00/-0.10                                                                           | Diameter (mm): |

|                                                                                                                    |                                                              |
|--------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------|
| 3.00                                                                                                               | Thickness (mm):                                              |
| Protective as needed                                                                                               | Bevel:                                                       |
| 12.7                                                                                                               | Maximum Edge Thickness (mm):                                 |
| 21° 10'                                                                                                            | Wedge Angle (arcmin):                                        |
| Optical Properties                                                                                                 |                                                              |
| ±30                                                                                                                | Angle Tolerance (arcsec):                                    |
| VIS-NIR (400-1000nm)                                                                                               | Coating:                                                     |
| 632.8                                                                                                              | Design Wavelength DWL (nm):                                  |
| N-BK7                                                                                                              | Substrate: <input type="checkbox"/>                          |
| 20-10                                                                                                              | Surface Quality:                                             |
| Beam Deviation                                                                                                     | Image Orientation:                                           |
| R <sub>abs</sub> ≤0.25% @ 880nm<br>R <sub>avg</sub> ≤1.25% @ 400 - 870nm<br>R <sub>avg</sub> ≤1.25% @ 890 - 1000nm | Coating Specification:                                       |
| 400 - 1000                                                                                                         | Wavelength Range (nm):                                       |
| 5 J/cm² @ 532nm, 10ns                                                                                              | Damage Threshold, By Design: <input type="checkbox"/>        |
| 0.50                                                                                                               | Power (fringes) @ 632.8nm:                                   |
| 0.20                                                                                                               | Irregularity (fringes) @ 632.8nm:                            |
| 12.00                                                                                                              | Ray Deviation @ 633nm (°):                                   |
| 21.26                                                                                                              | Power (diopters):                                            |
| 21.17°                                                                                                             | Wedge Angle (°):                                             |
| Material Properties                                                                                                |                                                              |
| 7.1                                                                                                                | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |
| Regulatory Compliance                                                                                              |                                                              |
| Compliant                                                                                                          | RoHS 2015:                                                   |
| View                                                                                                               | Certificate of Conformance:                                  |
| Compliant                                                                                                          | Reach 235:                                                   |


## Product Details

- Ideal for Beam Steering
- 0.5° - 15° Beam Deviation Options
- Available Uncoated or Anti-Reflection Coated
- [Anamorphic Prism Pair](#) Also Available

Wedge prisms can be used individually to deviate a laser beam a set angle, or two wedge prisms can be used together for beam steering applications. A single wedge prism's ability to deviate the angle of an incident beam is measured in Diopters with 1 diopter deviating the beam 1cm at a 1m working distance.

Two wedge prisms can be used as an anamorphic pair for beam shaping (to correct the elliptical shape of diode outputs). Wedge prisms can also be paired to steer a beam anywhere within a circle described by the full angle 4θ, where θ is the deviation from a single prism. This beam steering is accomplished by rotating the two wedge prisms independently of each other and is typically used to scan a beam to different locations in imaging applications.

Note: Beam deviation is shown in degrees and diopters. One diopter is 1cm of deviation at a distance of 1m from the prism.




## Technical Information

Beam Steering With Wedge Prisms



N-BK7


Uncoated N-BK7 Typical Transmission



Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra.

[Click Here to Download Data](#)

N-BK7 with  $\text{MgF}_2$  Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with  $\text{MgF}_2$  (400-700nm) coating at  $0^\circ$  AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{\text{avg}} \leq 1.75\% @ 400 - 700\text{nm}$  (N-BK7)

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with VIS-EXT Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at  $0^\circ$  AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{\text{avg}} \leq 0.5\% @ 350 - 700\text{nm}$





Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with VIS-NIR Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at  $0^\circ$  AOI.

|                                                                                                                                                                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                                                              | <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 0.25\% @ 880nm</math><br/><math>R_{avg} \leq 1.25\% @ 400 - 870nm</math><br/><math>R_{avg} \leq 1.25\% @ 890 - 1000nm</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                           |
| <p data-bbox="596 516 974 605"><b>N-BK7 with VIS 0° Coating</b><br/><b>Typical Transmission</b></p>        | <p>Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 0.4\% @ 425 - 675nm</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                          |
| <p data-bbox="569 1110 1037 1199"><b>N-BK7 with YAG-BBAR Coating</b><br/><b>Typical Transmission</b></p>  | <p>Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 0.25\% @ 532nm</math><br/><math>R_{abs} \leq 0.25\% @ 1064nm</math><br/><math>R_{avg} \leq 1.0\% @ 500 - 1100nm</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>           |
| <p data-bbox="617 1748 1010 1837"><b>N-BK7 with NIR I Coating</b><br/><b>Typical Transmission</b></p>     | <p>Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 0.5\% @ 600 - 1050nm</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                       |
| <p data-bbox="606 2386 1016 2475"><b>N-BK7 with NIR II Coating</b><br/><b>Typical Transmission</b></p>    | <p>Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 1.5\% @ 750 - 800nm</math><br/><math>R_{abs} \leq 1.0\% @ 800 - 1550nm</math><br/><math>R_{avg} \leq 0.7\% @ 750 - 1550nm</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p> |

|                 |     |     |     |      |      |      |      |      |      |  |
|-----------------|-----|-----|-----|------|------|------|------|------|------|--|
| 200             | 400 | 600 | 800 | 1000 | 1200 | 1400 | 1600 | 1800 | 2000 |  |
| Wavelength (nm) |     |     |     |      |      |      |      |      |      |  |

## Coating Curves

### Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

---