

[See all 22 Products in Family](#)

1.28mm FL CS-Mount, Auto Iris, Wide Angle Lens



1.28mm FL C-Mount, Manual Iris, Wide Angle Lens, #62-050



Stock #68-696 [CONTACT US](#)

- 1 + C\$1,218⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	C\$1,218.00 each
Need More?	Request Quote

Product Downloads

General

Product Family:
Low Distortion Wide Angle Lenses

Type:
Fixed Focal Length Lens

Style:
Auto Iris

Physical & Mechanical Properties

DC Auto Iris	Iris Option:
65.00	Length (mm):
36.0	Maximum Diameter (mm):
36	Outer Diameter (mm):
110.00	Weight (g):

Optical Properties

125°	Horizontal Field of View, 1/3" Sensor:
6.00	Maximum Image Circle (mm):
1.28	Focal Length FL (mm):
100 - ∞	Working Distance (mm):
f/1.8 - Closed	Aperture (f/#):
<3	Distortion (%):
<3	Maximum Distortion (%):
VIS	Lens Wavelength Range:

Sensor

1/3"	Maximum Sensor Format:
4.50	Pixel Size (µm):

Threading & Mounting

N/A	Filter Thread:
CS-Mount	Mount:

Regulatory Compliance

Exempt	RoHS 2015:
Contains SVHC(s)	Reach 223:
View	Certificate of Conformance:

Product Details

- Up to 1/2.5", C-Mount and CS-Mount options
- Up to 3 MegaPixel and Down to 1% Distortion
- No Refocusing from 100mm to Infinity
- 1.28mm to 40mm Focal Length

Low Distortion Wide Angle Lenses maintain high resolution for applications with long working distance requirements and can accommodate multi-megapixel camera sensors. The optical design of these low-distortion wide-angle lenses enables users to achieve less than 3% distortion over a 125° field of view, or less than 1% distortion over a 110° field of view. These lenses feature a locking screw for the manual iris enabling the use in high vibration environments. Low Distortion Wide Angle Lenses are ideal for security and surveillance, machine vision, or [factory automation](#) applications. These lenses do not require refocusing from 100mm to Infinity.

Note: Image will be flipped (180° rotation). Auto Iris Options require cameras with P-Iris or DC Iris control.