

**TECHSPEC® 12mm Dia. x 100mm FL 405nm V-Coat, UV PCX Lens**



TECHSPEC 405nm Laser Line Coated Fused Silica PCXLenses



Stock **#34-069** ☐ In Stock

[Other Coating Options](#)

1

**C\$179.90**

ADD TO CART

Qty 1-5

C\$179.90

Qty 6+

C\$143.85

Volume Pricing

[Request Quote](#)

Get Product Downloads



**Diameter (mm):**  
12.00 +0.0/-0.025

**Effective Focal Length EFL (mm):**

|                                                                                                  |
|--------------------------------------------------------------------------------------------------|
| 100.00 @587.6nm                                                                                  |
| <b>Back Focal Length BFL (mm):</b><br>98.33                                                      |
| <b>Coating:</b><br>Laser V-Coat (405nm)                                                          |
| <b>Coating Specification:</b><br>R <sub>abs</sub> <0.25% @ 405nm                                 |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">Fused Silica</a> (Corning 7980)        |
| <b>Surface Quality:</b><br>40-20                                                                 |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                                                            |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                                                      |
| <b>Focal Length Tolerance (%):</b><br>±1                                                         |
| <b>Centering (arcmin):</b><br>≤1                                                                 |
| <b>Center Thickness CT (mm):</b><br>2.44 ±0.05                                                   |
| <b>Edge Thickness ET (mm):</b><br>2.05                                                           |
| <b>Radius R<sub>1</sub> (mm):</b><br>45.85                                                       |
| <b>Clear Aperture CA (mm):</b><br>11                                                             |
| <b>f/#:</b><br>8.33                                                                              |
| <b>Numerical Aperture NA:</b><br>0.06                                                            |
| <b>Design Wavelength DWL (nm):</b><br>405                                                        |
| <b>Type:</b><br>Plano-Convex Lens                                                                |
| <b>Bevel:</b><br>Protective bevel as needed                                                      |
| <b>Edges:</b><br>Fine Ground, Protective Bevel as Needed                                         |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>3 J/cm <sup>2</sup> @405nm, 10ns |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |