


TECHSPEC® 12mm Diameter x 25mm FL, 1064nm Coated, Laser Grade PCX Lens



TECHSPEC Laser Grade PCXLenses

Stock **#67-970 8 In Stock**

Other Coating Options

-

1

+

C\$291<sup>20</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | C\$291.20 each                |
| Qty 6-25       | C\$232.40 each                |
| Qty 26-49      | C\$215.60 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Plano-Convex Lens

Physical & Mechanical Properties

Diameter (mm):

12.00 +0.00/-0.10


Centering (arcmin):

|                                  |                                  |
|----------------------------------|----------------------------------|
| <1                               |                                  |
| 3.92 ±0.05                       | Center Thickness CT (mm):        |
| 2.22                             | Edge Thickness ET (mm):          |
| 10.2                             | Clear Aperture CA (mm):          |
| Protective as needed             | Bevel:                           |
| Optical Properties               |                                  |
| 25.00 @ 587.6nm                  | Effective Focal Length EFL (mm): |
| 22.31                            | Back Focal Length BFL (mm):      |
| Laser V-Coat (1064nm)            | Coating:                         |
| R <sub>abs</sub> <0.25% @ 1064nm | Coating Specification:           |
| Fused Silica (Corning 7980)      | Substrate: □                     |
| 20-10                            | Surface Quality:                 |
| λ                                | Power (P-V) @ 632.8nm:           |
| λ/10                             | Irregularity (P-V) @ 632.8nm:    |
| ±1                               | Focal Length Tolerance (%):      |
| 11.46                            | Radius R <sub>1</sub> (mm):      |
| 2.08                             | f/#:                             |
| 0.24                             | Numerical Aperture NA:           |
| 1064                             | Design Wavelength DWL (nm):      |
| 15 J/cm² @ 1064nm, 20ns, 20Hz    | Damage Threshold, By Design: □   |
| Regulatory Compliance            |                                  |
| Compliant                        | RoHS 2015:                       |
| Compliant                        | REACH 201:                       |
| View                             | Certificate of Conformance:      |



## Product Details

- Guaranteed Laser Damage Threshold
- 10-5 Surface Quality
- λ/10 Surface Accuracy

TECHSPEC® Laser Grade PCXLenses are designed for high energyNd:YAG laser applications including laser cutting, machining, and welding. The precision fused silica substrate, featuring λ/10 surface accuracy and 10-5 surface quality, ensures low scatter and excellent transmitted wavefront performance. TECHSPEC® Laser Grade PCXLenses are available uncoated or with a variety of high laser damage threshold anti-reflection (AR) coating options. Coatings are available at the most common Nd:YAG laser wavelengths to ensure maximum laser throughput.



## Technical Information



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts