

TECHSPEC[®] 1310nm, 76.2mm Dia. x 12.7mm Thickness, Ultrafast Laser Mirror



Stock #73-725 NEW [CONTACT US](#)

-

1

+

C\$1,295^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$1,295.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Laser Mirror

Type:

Physical & Mechanical Properties

76.20 +0.00/-0.10

Diameter (mm):

6.35 ±0.20	Thickness (mm):
<3	Parallelism (arcmin):
90	Clear Aperture (%):

Commercial Polish	Back Surface:
-------------------	---------------

Optical Properties

45	Angle of Incidence (°):
Ultrafast (1260 - 1360nm)	Coating:

1310	Design Wavelength DWL (nm):
Fused Silica	Substrate:

10-5	Surface Quality:
R _(avg) S & P >99.90% @ 1310nm @ 45° AOI R _(avg) >99.7% @ 1260 - 1360nm @ 45° AOI	Coating Specification:

1260 - 1360	Wavelength Range (nm):
λ/8	Surface Flatness (P-V):

Dielectric	Coating Type:
±20 fs ² @ 1260 – 1360nm @ 45° AOI (s-pol) ±30 fs ² @ 1285 – 1335 nm @ 45° AOI (p-pol)	GDD Specification:

Environmental & Durability Factors

ML-PRF-13830B	Durability:
---------------	-------------

Regulatory Compliance

View	Certificate of Conformance:
------	-----------------------------

PRODUCT DETAILS

- GDD as Low as ±20fs² at Design Wavelength Range
 - Greater than 99.9% Reflectivity
 - Ideal for Ti:sapphire and Yb:doped Ultrafast Lasers
- TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors feature a multilayer dielectric coating on fused silica substrates for excellent reflectivity of greater than 99.9%, and low coefficient of thermal expansion, making them ideal for ultrafast beam transport applications. These mirrors have a group delay dispersion (GDD) of near zero at their design wavelength range, minimizing dispersion of the reflected beam. TECHSPEC® Low GDD Dielectric Ultrafast Laser Mirrors are ideal for utilizing the first and second harmonic of Ti:sapphire and Yb:doped lasers for applications such as laser machining and welding.
- Note:** Please [contact us](#) if your application requires a TECHSPEC Low GDD Ultrafast Mirror with a custom wavelength, angle, or size.

CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).