

[All Products](#) / [Optics](#) / [Optical Assemblies](#) / [Laser Optic Assemblies](#) / [LightPath® Fiber Optic Collimators](#)

[See all 69 Products in Family](#)

LightPath 355110 | 1310nm Alignment, 0.40 NA Fiber Collimator w/ SMA Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock #64-776 CLEARANCE ☐ In Stock

1 **C\$165.13**

ADD TO CART

Qty 1+

C\$165.13

Volume Pricing

[Request Quote](#)

Get Product Downloads

Effective Focal Length EFL (mm):
6.24 @ 780nm

Numerical Aperture NA:
0.40

Substrate: ☐
[D-ZLaF52LA](#)

Coating:

BBAR (1050-1600nm)
Coating Specification: R _{abs} <1.0% @ 1050 - 1600nm
Surface Quality: 40-20
Clear Aperture CA (mm): 5.00
f/#: 1.25
Bevel: Protective bevel as needed
Connector: SMA
Construction: 304L Stainless Steel Housing
Housing Diameter (mm): 11.00
Housing Length (mm): 13.00
Lightpath Lens Code: 355110
Mount: M11 x0.5
Type: Fiber Collimator
Wavelength Range (nm): 1050 - 1600
Conjugate Distance: Infinite
Lens Included: #87-127
Alignment Wavelength (nm): 1310

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
