

[See all 22 Products in Family](#)

1.3mm FL, C-Mount, Manual Iris, Wide Angle Lens



Image represents #22-793; Design will vary by stock number.

Stock **#22-793** **1 In Stock**

⊖ 1 ⊕ C\$1,841⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$1,841.00 each
Need More?	Request Quote

Product Downloads

General

Product Family:
Low Distortion Wide Angle Lenses

Type:
Fixed Focal Length Lens

Physical & Mechanical Properties

Iris Option:
Variable

Length (mm):
55.00

36 **Maximum Diameter (mm):**

36 **Outer Diameter (mm):**

99 **Weight (g):**

Optical Properties

135° **Horizontal Field of View @ Max Sensor Format:**

109° **Horizontal Field of View, 1/3" Sensor:**

7.20 **Maximum Image Circle (mm):**

1.30 **Focal Length FL (mm):**

300 - ∞ **Working Distance (mm):**

F/1.8 - Closed **Aperture (f/#):**

<3 **Distortion (%):**

<3 **Maximum Distortion (%):**

VIS **Lens Wavelength Range:**

Sensor

1/2.5" **Maximum Sensor Format:**

4.50 **Pixel Size (µm):**

Threading & Mounting

N/A **Filter Thread:**

C-Mount **Mount:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Up to 1/2.5", C-Mount and CS-Mount options
- Up to 3 MegaPixel and Down to 1% Distortion
- No Refocusing from 100mm to Infinity
- 1.28mm to 40mm Focal Length

Low Distortion Wide Angle Lenses maintain high resolution for applications with long working distance requirements and can accommodate multi-megapixel camera sensors. The optical design of these low-distortion wide-angle lenses enables users to achieve less than 3% distortion over a 125° field of view, or less than 1% distortion over a 110° field of view. These lenses feature a locking screw for the manual iris enabling the use in high vibration environments. Low Distortion Wide Angle Lenses are ideal for security and surveillance, machine vision, or [factory automation](#) applications. These lenses do not require refocusing from 100mm to Infinity.

Note: Image will be flipped (180° rotation). Auto Iris Options require cameras with P-Iris or DC Iris control.