

[See all 22 Products in Family](#)

1.3mm FL, C-Mount, Manual Iris, Wide Angle Lens



Image represents #22-793; Design will vary by stock number.

Stock **#22-793** 1 In Stock

-

1

+

C\$1,841⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$1,841.00 each
Need More?	Request Quote

Product Downloads

General	
Low Distortion Wide Angle Lenses	Series:
Fixed Focal Length Lens	Type:
Physical & Mechanical Properties	
Manual Iris	Iris Option:
55.00	Length (mm):

36	Maximum Diameter (mm):
36	Outer Diameter (mm):
99	Weight (g):
Optical Properties	
135	Horizontal Field of View @ Max Sensor Format:
109°	Horizontal Field of View, 1/3" Sensor:
7.20	Maximum Image Circle (mm):
1.30	Focal Length FL (mm):
300 - ∞	Working Distance (mm):
F/1.8 - Closed	Aperture (f/#):
<3	Distortion (%):
<3	Maximum Distortion (%):
VS	Lens Wavelength Range:
Sensor	
1/2.5"	Maximum Sensor Format:
4.50	Pixel Size (µm):
Threading & Mounting	
N/A	Filter Thread:
C-Mount	Mount:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Up to 1/2.5", C-Mount and CS-Mount options
- Up to 3 MegaPixel and Down to 1% Distortion
- No Refocusing from 100mm to Infinity
- 1.28mm to 40mm Focal Length

Low Distortion Wide Angle Lenses maintain high resolution for applications with long working distance requirements and can accommodate multi-megapixel camera sensors. The optical design of these low-distortion wide-angle lenses enables users to achieve less than 3% distortion over a 125° field of view, or less than 1% distortion over a 110° field of view. These lenses feature a locking screw for the manual iris enabling the use in high vibration environments. Low Distortion Wide Angle Lenses are ideal for security and surveillance, machine vision, or [factory automation](#) applications. These lenses do not require refocusing from 100mm to Infinity.

Note: Image will be flipped (180° rotation). Auto Iris Options require cameras with P-Iris or DC Iris control.