

14um Photoconductive Detector, PCI-3TE-12-1x1-TO8-wZnSeAR-36



14um Photoconductive Detector, PCI-3TE-12-1x1-TO8-wZnSeAR-36

Stock #90-463 NEW 4 In Stock

-

1

+

C\$2,786⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$2,786.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

IR Photoconductive Detector

Type:

PCI-3TE-12-1x1-TO8-wZnSeAR-36

Model Number:

TO-8

Package:

Vigo Photonics

Manufacturer:

Physical & Mechanical Properties	
7	Weight (g):
1.00 x 1.00	Active Area (mm):
Optical Properties	
14000	Spectral Response (nm):
36	Acceptance Angle (°):
Environmental & Durability Factors	
-20 to +30	Operating Temperature (°C):
-20 to +50	Storage Temperature (°C):
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

Product Details

- Mid and Long-Wave Infrared (MMIR/LWIR) Spectral Range
- 1 × 1mm² Active Areas with Acceptance Angles up to 90°
- TO-39 and TO-8 Package Styles with Specialized Anti-Reflection Windows

Vigo Photonics Infrared Detectors deliver high-performance mid and long-wave IR detection with exceptional sensitivity and stability across demanding applications. These HgCdTe and InAsSb detectors are available with a variety of cooling configurations, including single, dual, triple, and quad-stage thermoelectric coolers, to optimize signal-to-noise ratios. Models are offered with active areas of 1 × 1mm² and acceptance angles up to 90°, providing flexibility for system integration. Vigo Photonics Infrared Detectors feature precision packaging options such as TO-39 and TO-8 housings with specialized anti-reflection coatings for maximum throughput. These detectors combine reliability with infrared technology, making them ideal for spectroscopy, gas analysis, and defense applications.