

TECHSPEC®

15.0mm Dia. x 40.0mm FL, MgF₂ Coated, Inked, Plano-Convex Lens



Stock **#45-096-INK** 3-5 DAYS

[Other Coating Options](#)

- 1 +

C\$63.00

ADD TO CART

Qty 1-9
C\$63.00
Qty 10+
C\$56.70
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
15.00 ±0.025

Effective Focal Length EFL (mm):
40.00 @ 587.6nm

Back Focal Length BFL (mm): 38.02
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 1.59
Radius R₁ (mm): 20.67
Clear Aperture CA (mm): 14
f/#: 2.67
Numerical Aperture NA: 0.19
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View