

White, MicroBrite Ultra High Intensity Bar Light

See More by [Advanced Illumination](#)



Advanced Illumination MicroBrite Ultra High Intensity Bar Light

Stock **#18-540** **1 In Stock**

-

1

+

C\$861^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$861.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS


General	
AL295-150WHIIC	Model Number:
50,000	LED Lifetime (hours):
Type of Illumination:	

LED Illuminator	
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available	
Advanced Illumination	Manufacturer:
Bar Light	Geometry:
Constant	Illumination Mode:
Physical & Mechanical Properties	
165.6 x 20.1 x 20.1	Dimensions (mm):
68.9	Weight (g):
Optical Properties	
White	Color:
Electrical	
0.27A	Maximum Input Current:
Hardware & Interface Connectivity	
Flying Leads	Connector:
24V	Input Voltage (V):
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	
Environmental & Durability Factors	
0 - 60	Operating Temperature (°C):
IP50	Environmental Rating:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 233:

PRODUCT DETAILS

- High Intensity Output up to 73,000 Lux
 - Compact Housing with T-Slot Mount
 - Full Range of Wavelengths Available
 - Optional Manual Intensity Adjustments ([#86-887](#) and [#89-555](#)) Recommended
- Advanced Illumination MicroBrite Ultra High Intensity Bar Lights offer high performance machine vision lights in a compact form factor. With a high intensity output of 73,000 Lux at a working distance of 100mm, these MicroBrite Bar Lights outperform higher cost comparable bar lights. These bar lights are available in the most common machine vision wavelengths. Advanced Illumination MicroBrite Ultra High Intensity Bar Lights are designed for applications requiring intense illumination for large area inspection. Please contact us if your application requires a MicroBrite Ultra High Intensity Bar Light with a custom length.
- Note:** Requires 24V power supply [#66-855](#). Manual Intensity Adjustment [#86-887](#) and [#89-555](#) are recommended and sold separately.

3D-Printable Mount Files



Bar or Line Light Configuration

**DOWNLOAD
NOW**

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to 1/4-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



Application Note

Illumination Mounts for Machine Vision Applications
[Read](#) 



Video

Assembly of 3D Printed Mounts for Common Illumination Geometries
[Watch](#) 