

## 1550nm, $\lambda/2$ Precision Zero Order Retarder



Stock #49-217 **3 In Stock**

- 1 + C\$1,057<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-5	C\$1,057.00 each
Qty 6+	C\$840.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Polymer Waveplate **Type:**

### Physical & Mechanical Properties

10.16 **Clear Aperture CA (mm):**

25.40 **Diameter (mm):**

±0.508	Thickness Tolerance (mm):
±0.127	Dimensional Tolerance (mm):
Birefringent Polymer Stack	Construction:

## Optical Properties

1550	Design Wavelength DWL (nm):
Polymer Film on <a href="#">N-BK7</a>	Substrate: <input type="checkbox"/>
0.5	Reflection (%):
$\lambda/2$	Retardance:
40-20	Surface Quality:
$\leq \lambda/5$ @ 632.8nm	Transmitted Wavefront, RMS:
$\lambda/350$	Retardance Tolerance:
1.00	Beam Deviation (arcmin):
500 W/cm <sup>2</sup>	Damage Threshold, By Design: <input type="checkbox"/>
0	Retardance Order:

## Threading & Mounting

6.35	Mount Thickness (mm):
------	-----------------------

## Environmental & Durability Factors

-20 to +50	Operating Temperature (°C):
------------	-----------------------------

## Regulatory Compliance

<a href="#">Compliant</a>	RoHS 2015:
<a href="#">View</a>	Certificate of Conformance:
<a href="#">Compliant</a>	REACH 241:

## Product Details

- $\lambda/4$  and  $\lambda/2$  Retardance
- Excellent Angular Field of View
- Birefringent Polymer Stack
- High Damage Threshold of 500 W/cm<sup>2</sup>

Precision Zero Order Waveplates (Retarders) feature carefully aligned birefringent polymer sheets laminated between two precision N-BK7 windows, and are available in standard  $\lambda/4$  and  $\lambda/2$  options for common visible and NIR wavelengths. These polymer waveplates (retarders) offer excellent angular field of view because they are true zero-order retarders. Also, they will experience less than 1% retardance change over a  $\pm 10^\circ$  angle of incidence. Each Precision Zero Order Waveplates (Retarders) is mounted in a metal ring with the fast axis clearly marked.