

TECHSPEC® 1.5X, 266nm Vega® Nd:YAG Laser Line Beam Expander



TECHSPEC® Vega™ Laser Line Beam Expanders



Stock **#12-872** ☐ In Stock

- 1 +

C\$494.20

ADD TO CART

Qty 1-9
C\$494.20

Qty 10+
C\$434.00

Volume Pricing
[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):
0

Coating:
Laser V-Coat (266nm)

Design Wavelength DWL (nm): 266
Entrance Aperture (mm): 10
Exit Aperture (mm): 23
Expansion Power: 1.5X
Substrate: Fused Silica (Corning 7980)
Length (mm): 77.30
Mounting Threads: Input: Male M30 x1 Output: Female M27 x0.5
Transmission (%): >99 (nominal)
Type: Beam Expander
Weight (g): 75
Housing Diameter (mm): 29.95
Transmitted Wavefront, P-V: <λ/10 for 4mm input beam (nominal, <λ= DWL)
Coating Specification: R_{abs} <0.25% @ 266nm
Wavelength Range (nm): 250 - 280
Style: Fixed Magnification
Damage Threshold, By Design: 1.5 J/cm² @ 266nm, 10ns, 20Hz
Divergence Adjustment: Rotating Optics

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View