

[See all 23 Products in Family](#)

**TECHSPEC® 30 x 30mm  $\lambda/10$  ZERODUR® Uncoated Mirror Substrate**



Stock #71-517 **1 In Stock**

⊖ 1 ⊕ C\$179<sup>20</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	C\$179.20 each
Qty 6-25	C\$143.36 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Mirror Substrate **Type:**

**Physical & Mechanical Properties**

5.00 ±0.20 **Thickness (mm):**

30.0 x 30.0 +0.00/-0.20 **Dimensions (mm):**

Commercial Polish **Back Surface:**

Protective as needed	<b>Bevel:</b>
90	<b>Clear Aperture (%):</b>
Ground	<b>Edges:</b>
30.00	<b>Length (mm):</b>
30.00	<b>Width (mm):</b>
30	<b>Parallelism (arcsec):</b>

### Optical Properties

Uncoated	<b>Coating:</b>
$\lambda/10$	<b>Surface Flatness (P-V):</b>
ZERODUR®	<b>Substrate:</b> <input type="checkbox"/>
20-10	<b>Surface Quality:</b>

### Material Properties

0.1	<b>Coefficient of Thermal Expansion CTE (<math>10^{-6}/^{\circ}\text{C}</math>):</b>
-----	--

### Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------

## Product Details

- Precision ZERODUR® Substrates
- $\lambda/10$  Flatness
- Low Coefficient of Thermal Expansion

TECHSPEC® ZERODUR Mirror Substrates are well suited for applications where temperature fluctuation is a concern. The ZERODUR® substrates have a coefficient of thermal expansion (CTE) of  $\pm 0.10 \times 10^{-6}/^{\circ}\text{C}$ , which is an order of magnitude lower than most glass types. The low CTE allows these mirrors to have a consistent reflected wavefront, even when exposed to environments with varying temperature or illumination sources with changing intensity. TECHSPEC® ZERODUR Mirror Substrates feature precision polished substrates with  $\lambda/10$  flatness and 20-10 surface quality.