

1.5mm Dia. x 1.0mm FL, Telecom-NIR Coated, Plano-Convex Lens



Stock **#45-968** CLEARANCE ☐ **In Stock**

[Other Coating Options](#)

1

C\$30.73

ADD TO CART

Qty 1+
C\$30.73

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
1.50 +0.00/-0.05

Effective Focal Length EFL (mm):
1.00 @ 587.6nm

Back Focal Length BFL (mm):
0.57

Coating:
Telecom-NIR

Coating Specification:
R_{abs} ≤0.25% @ 1295 - 1325nm

R _{abs} ≤0.25% @ 1535 - 1565nm R _{avg} ≤0.25% @ 1200 - 1600nm
Substrate: 
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): 30-45
Center Thickness CT (mm): 0.80 ±0.05
Edge Thickness ET (mm): 0.35
Radius R ₁ (mm): 0.85
Clear Aperture CA (mm): 1.35
f/#: 0.67
Numerical Aperture NA: 0.75
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 1200 - 1600

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View