

[See all 5 Products in Family](#)

## 15mm Dia. x 30mm FL, Commercial Grade, Plano-Convex Lens



Stock #23-085 CLEARANCE **20+ In Stock**

- 1 + C\$28<sup>.70</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	C\$28.70 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Plano-Convex Lens **Type:**

#### Physical & Mechanical Properties

15.00 +0.00/-0.10 **Diameter (mm):**

6.00 **Centering (arcmin):**

1.27 **Edge Thickness ET (mm):**

**Clear Aperture CA (mm):**

## Optical Properties

Effective Focal Length EFL (mm):

30.00

Coating:

MgF<sub>2</sub> (400-700nm)

Coating Specification:

R<sub>avg</sub> ≤ 1.75% @ 400 - 700nm

Substrate: □

N-SK18

Focal Length Tolerance (%):

±1

Radius R<sub>1</sub> (mm):

19.16

f#:

2.00

Numerical Aperture NA:

0.25

## Regulatory Compliance

Certificate of Conformance:



[View](#)

## Product Details

- Feature Standard Designs and Specifications
- Also Available [Uncoated](#)
- For More Options, View [Precision Quality Plano-Convex \(PCX\) Lenses](#)

Plano convex lenses (PCX) have one flat and one outward curving face and a positive focal length. They are ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. MgF<sub>2</sub> anti-reflection coating offers improved transmission in the visible spectrum. Commercial Grade MgF<sub>2</sub> Coated Plano-Convex (PCX) Lenses offer commercial quality, at an affordable price.

## Technical Information



## Coating Curves