

15mm Dia. x 22.5mm FL, Commercial Grade, Plano-Convex Lens



Stock **#23-083** CLEARANCE **20+ In Stock**

-

1

+

C\$28^{.70}

ADD TO CART

Volume Pricing	
Qty 1+	C\$28.70 each
Need More?	Request Quote

Product Downloads

General

	Type:
Plano-Convex Lens	

Physical & Mechanical Properties

15.00 +0.00/-0.10	Diameter (mm):
6.00	Centering (arcmin):
1.39	Edge Thickness ET (mm):
	Clear Aperture CA (mm):

Optical Properties

Effective Focal Length EFL (mm):
22.50

Back Focal Length BFL (mm):
20.37

Coating:
MgF₂ (400-700nm)

Coating Specification:
R_{avg} ≤1.75% @400 - 700nm

Substrate: ☐
N-SK18

Focal Length Tolerance (%):
±1

Radius R₁ (mm):
14.37

f#:
1.5

Numerical Aperture NA:
0.33

Regulatory Compliance


Certificate of Conformance:
[View](#)

Product Details

- Feature Standard Designs and Specifications
- Also Available [Uncoated](#)
- For More Options, View [Precision Quality Plano-Convex \(PCX\) Lenses](#)

Plano convex lenses (PCX) have one flat and one outward curving face and a positive focal length. They are ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. MgF₂ anti-reflection coating offers improved transmission in the visible spectrum. Commercial Grade MgF₂ Coated Plano-Convex (PCX) Lenses offer commercial quality, at an affordable price.

Technical Information



Coating Curves